
# 23150630601 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Pfannenberg PROTECT PRO 10-SIL series audible signal horn, 116 dB at 1m, 340 Hz to 2.9 kHz tone frequency, (80) selectable tone(s), 10–60 VDC, surface mount, aluminum housing, red, IP66 and IP67, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/23150630601

## Technical Specifications

| | |
|---|---|
| **Brand** | Pfannenberg |
| **Item** | Audible signal horn |
| **Series** | PROTECT PRO 10-SIL |
| **Loudness Decibel** | 116 dB at 1m |
| **Tone Frequency** | 340 Hz to 2.9 kHz |
| **Tone Type** | (80) selectable |
| **Touch to Acknowledge** | No |
| **Number of Alarms** | 80 |
| **Voltage Rating** | 10–60 VDC |

| | |
|---|---|
| **Mounting** | Surface |
| **Housing Material** | Aluminum |
| **Color** | Red |
| **IP Rating** | IP66 and IP67 |
| **NEMA Rating** | 4/4X |
| **Connection** | Screw terminal |
| **Additional Information** | Machine & Functional Safety (SIL), hazardous location, explosion proof rated |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | S7256 |
| **UL Recognized File #** | NONE |
| **UL Hazardous File #** | NONE |
| **CE** | View CE declarations |
| **CSA File #** | NONE |
| **RoHS Status** | Yes with Exemptions (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/23150630601.pdf
See store item page for other formats.