23150640000 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Pfannenberg PROTECT PRO 10 series audible signal horn, 116 dB at 1m, 340 Hz to 2.9 kHz tone frequency, (80) selectable tone(s), 95–265 VAC, surface mount, aluminum housing, red, IP66 and IP67, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/23150640000

Technical Specifications

Brand	Pfannenberg
Item	Audible signal horn
Series	PROTECT PRO 10
Loudness Decibel	116 dB at 1m
Tone Frequency	340 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Number of Alarms	80

Voltage Rating	95–265 VAC
Mounting	Surface
Housing Material	Aluminum
Color	Red
IP Rating	IP66 and IP67
NEMA Rating	4/4X
Connection	Screw terminal

Agency Approvals

UL Listed File #	S7256
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes with Exemptions (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/23150640000.pdf
See store item page for other formats.