23151635007 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Pfannenberg PROTECT PRO L 10–3G / 3D series LED audible-visual signal beacon, 116 dB at 1m, (80) selectable tone(s), selectable permanent, blinking or flashing, red, 214 x 167 x 148mm, 10–60 VDC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/23151635007

Technical Specifications

Brand	Pfannenberg
Item	Audible-visual signal beacon
Series	PROTECT PRO L 10–3G / 3D
Bulb Type	LED
Operator Size	214 x 167 x 148mm
Operator Color	Red
Light Color(s)	Red
Light Function	Selectable permanent, blinking or flashing
Housing Material	Aluminium/ABS plastic
Material	Aluminium/ABS plastic
Loudness Decibel	116 dB at 1m

Tone Frequency	150 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Number of Alarms	80
Voltage Rating	10–60 VDC
Mounting	Surface
IP Rating	IP66
NEMA Rating	4/4X
Connection	Screw terminal
Additional Information	Hazardous location, explosion proof rated

Agency Approvals

UL Listed File #	E542096
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes with Exemptions (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/23151635007.pdf
See store item page for other formats.