# 23151647007 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Pfannenberg PROTECT PRO L 10–3G / 3D series LED audible-visual signal beacon, 116 dB at 1m, (80) selectable tone(s), selectable permanent, blinking or flashing, blue, 214 x 167 x 148mm, 95–265 VAC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/23151647007

## Technical Specifications

| | |
|---|---|
| **Brand** | Pfannenberg |
| **Item** | Audible-visual signal beacon |
| **Series** | PROTECT PRO L 10–3G / 3D |
| **Bulb Type** | LED |
| **Operator Size** | 214 x 167 x 148mm |
| **Operator Color** | Blue |
| **Light Color(s)** | Blue |
| **Light Function** | Selectable permanent, blinking or flashing |
| **Housing Material** | Aluminium/ABS plastic |
| **Material** | Aluminium/ABS plastic |
| **Loudness Decibel** | 116 dB at 1m |

| | |
|---|---|
| **Tone Frequency** | 150 Hz to 2.9 kHz |
| **Tone Type** | (80) selectable |
| **Touch to Acknowledge** | No |
| **Number of Alarms** | 80 |
| **Voltage Rating** | 95–265 VAC |
| **Mounting** | Surface |
| **IP Rating** | IP66 |
| **NEMA Rating** | 4/4X |
| **Connection** | Screw terminal |
| **Additional Information** | Hazardous location, explosion proof rated |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E542096 |
| **UL Recognized File #** | NONE |
| **UL Hazardous File #** | NONE |
| **CE** | View CE declarations |
| **CSA File #** | NONE |
| **RoHS Status** | Yes with Exemptions (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/23151647007.pdf
See store item page for other formats.