

# 23310630101 Cut Sheet



Pfannenberg PATROL series audible signal horn, 105 dB at 1m, 150 Hz to 2.9 kHz tone frequency, (80) selectable tone(s), 10-57 VDC, surface mount, ABS/polycarbonate housing, gray, IP66, NEMA 4/4X. Requires 4-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23310630101>

## Technical Specifications

|                      |                     |
|----------------------|---------------------|
| Brand                | Pfannenberg         |
| Item                 | Audible signal horn |
| Series               | PATROL              |
| Loudness Decibel     | 105 dB at 1m        |
| Tone Frequency       | 150 Hz to 2.9 kHz   |
| Tone Type            | (80) selectable     |
| Touch to Acknowledge | No                  |
| Number of Alarms     | 80                  |

|                  |                        |
|------------------|------------------------|
| Voltage Rating   | 10-57 VDC              |
| Mounting         | Surface                |
| Housing Material | ABS/polycarbonate      |
| Color            | Gray                   |
| IP Rating        | IP66                   |
| NEMA Rating      | 4/4X                   |
| Requires         | 4-pin female M12 cable |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | S7256                                  |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/23310630101.pdf>  
See store item page for other formats.