

23350630055 Cut Sheet



Pfannenberg PATROL series audible signal horn, 107 dB at 1m, 150 Hz to 2.9 kHz tone frequency, (80) selectable tone(s), 10-57 VDC, surface mount, ABS/polycarbonate housing, gray, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23350630055>

Technical Specifications

| | |
|----------------------|---------------------|
| Brand | Pfannenberg |
| Item | Audible signal horn |
| Series | PATROL |
| Loudness Decibel | 107 dB at 1m |
| Tone Frequency | 150 Hz to 2.9 kHz |
| Tone Type | (80) selectable |
| Touch to Acknowledge | No |
| Number of Alarms | 80 |
| Voltage Rating | 10-57 VDC |
| Mounting | Surface |
| Housing Material | ABS/polycarbonate |
| Color | Gray |
| IP Rating | IP66 |
| NEMA Rating | 4/4X |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | S7256 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/23350630055.pdf>
See store item page for other formats.