

# 23350630055 Cut Sheet



Pfannenberg PATROL series audible signal horn, 107 dB at 1m, 150 Hz to 2.9 kHz tone frequency, (80) selectable tone(s), 10-57 VDC, surface mount, ABS/polycarbonate housing, gray, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23350630055>

## Technical Specifications

<b>Brand</b>	Pfannenberg
<b>Item</b>	Audible signal horn
<b>Series</b>	PATROL
<b>Loudness Decibel</b>	107 dB at 1m
<b>Tone Frequency</b>	150 Hz to 2.9 kHz
<b>Tone Type</b>	(80) selectable
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	10-57 VDC
<b>Mounting</b>	Surface
<b>Housing Material</b>	ABS/polycarbonate
<b>Color</b>	Gray
<b>IP Rating</b>	IP66
<b>NEMA Rating</b>	4/4X

## Agency Approvals

<b>UL Listed File #</b>	S7256
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/23350630055.pdf>  
See store item page for other formats.