

23351805055 Cut Sheet



Pfannenberg PATROL series Xenon tube audible-visual signal beacon, 107 dB at 1m, (80) selectable tone(s), flashing strobe (1 Hz flash frequency), red, 163 x 132 x 215mm, 24 VDC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23351805055>

Technical Specifications

Brand	Pfannenberg
Item	Audible-visual signal beacon
Series	PATROL
Bulb Type	Xenon tube
Operator Size	163 x 132 x 215mm
Operator Color	Red
Light Color(s)	Red
Light Function	Flashing strobe (1 Hz flash frequency)
Housing Material	Polycarbonate

Material	ABS plastic
Loudness Decibel	107 dB at 1m
Tone Frequency	150 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Voltage Rating	24 VDC
Mounting	Surface
IP Rating	IP66
NEMA Rating	4/4X

Agency Approvals

UL Listed File #	S7256
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/23351805055.pdf>
See store item page for other formats.