

# 23353638055 Cut Sheet



Pfannenberg PATROL series LED audible-visual signal beacon, 107 dB at 1m, (80) selectable tone(s), selectable permanent, blinking or flashing, red/yellow/green/blue, 163 x 132 x 215mm, 12-48 VDC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23353638055>

## Technical Specifications

Brand	Pfannenberg
Item	Audible-visual signal beacon
Series	PATROL
Bulb Type	LED
Operator Size	163 x 132 x 215mm
Operator Color	Clear
Light Color(s)	Red/yellow/green/blue
Light Function	Selectable permanent, blinking or flashing
Housing Material	Polycarbonate
Material	ABS plastic

Loudness Decibel	107 dB at 1m
Tone Frequency	150 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Number of Alarms	80
Voltage Rating	12-48 VDC
Mounting	Surface
IP Rating	IP66
NEMA Rating	4/4X

## Agency Approvals

UL Listed File #	S7256
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/23353638055.pdf>  
See store item page for other formats.