

# 23360630055 Cut Sheet



Pfannenberg PATROL series audible signal horn, 117 dB at 1m, 150 Hz to 2.9 kHz tone frequency, (80) selectable tone(s), 10-60 VDC, surface mount, ABS/polycarbonate housing, gray, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23360630055>

## Technical Specifications

Brand	Pfannenberg
Item	Audible signal horn
Series	PATROL
Loudness Decibel	117 dB at 1m
Tone Frequency	150 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Number of Alarms	80
Voltage Rating	10-60 VDC
Mounting	Surface
Housing Material	ABS/polycarbonate
Color	Gray
IP Rating	IP66
NEMA Rating	4/4X

## Agency Approvals

UL Listed File #	S7256
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/23360630055.pdf>  
See store item page for other formats.