

23361157055 Cut Sheet



Pfannenberg PATROL series Xenon tube audible-visual signal beacon, 117 dB at 1m, (80) selectable tone(s), flashing strobe (1 Hz flash frequency), blue, 214 x 156 x 270mm, 115 VAC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23361157055>

Technical Specifications

Brand	Pfannenberg
Item	Audible-visual signal beacon
Series	PATROL
Bulb Type	Xenon tube
Operator Size	214 x 156 x 270mm
Operator Color	Blue
Light Color(s)	Blue
Light Function	Flashing strobe (1 Hz flash frequency)
Housing Material	Polycarbonate
Material	ABS plastic

Loudness Decibel	117 dB at 1m
Tone Frequency	150 Hz to 2.9 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Number of Alarms	80
Voltage Rating	115 VAC
Mounting	Surface
IP Rating	IP66
NEMA Rating	4/4X

Agency Approvals

UL Listed File #	S7256
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/23361157055.pdf>
See store item page for other formats.