

23361804055 Cut Sheet



Pfannenberg PATROL series Xenon tube audible-visual signal beacon, 117 dB at 1m, (80) selectable tone(s), flashing strobe (1 Hz flash frequency), amber, 214 x 156 x 270mm, 24 VDC, IP66, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23361804055>

Technical Specifications

| | |
|-------------------------|--|
| Brand | Pfannenberg |
| Item | Audible-visual signal beacon |
| Series | PATROL |
| Bulb Type | Xenon tube |
| Operator Size | 214 x 156 x 270mm |
| Operator Color | Amber |
| Light Color(s) | Amber |
| Light Function | Flashing strobe (1 Hz flash frequency) |
| Housing Material | Polycarbonate |

| | |
|-----------------------------|-------------------|
| Material | ABS plastic |
| Loudness Decibel | 117 dB at 1m |
| Tone Frequency | 150 Hz to 2.9 kHz |
| Tone Type | (80) selectable |
| Touch to Acknowledge | No |
| Voltage Rating | 24 VDC |
| Mounting | Surface |
| IP Rating | IP66 |
| NEMA Rating | 4/4X |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | S7256 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/23361804055.pdf>
See store item page for other formats.