

235122-2 Cut Sheet



RUKO hand tap, M12 x 1.0 fine, square shank per DIN 10, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/235122-2>

Technical Specifications

Brand	RUKO
Item	Hand tap
Thread	M12 x 1.0 fine threads per DIN 2181
Thread Length	20mm
Overall Length	2.8in (71mm)
Tap Drill Size	11mm
Shank	Square shank per DIN 10
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Thread making

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document