

24029055 Cut Sheet



WERMA MC55 Touch series LED audible-visual signal beacon, 85 dB at 1m, continuous tone(s), touch to acknowledge, permanent, red/yellow/green, 55mm, 24 VDC, IP65 and IP69K, NEMA 4X. Requires 5-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/24029055>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	MC55 Touch
Bulb Type	LED
Operator Size	55mm
Operator Color	White
Light Color(s)	Red/yellow/green
Light Function	Permanent
Housing Material	Polycarbonate
Material	Polycarbonate
Loudness Decibel	85 dB at 1m

Tone Frequency	3480 Hz
Tone Type	Continuous
Touch to Acknowledge	Yes
Voltage Rating	24 VDC
Mounting	M30 x 1.5
IP Rating	IP65 and IP69K
NEMA Rating	4X
Connection	5-pin M12 quick-disconnect
Requires	5-pin female M12 cable
Additional Information	PNP connection

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/24029055.pdf>
See store item page for other formats.