

24032050 Cut Sheet



WERMA MC55 series LED industrial signal beacon, 55mm, red/ yellow/green/blue/turquoise/violet/white, permanent, IP65 and IP69K, NEMA 4X, M30 x 1.5 mount, 10–30 VDC. Requires 5-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/24032050>

Technical Specifications

Brand	WERMA
Item	Industrial signal beacon
Bulb Type	LED
Series	MC55
Operator Size	55mm
Operator Color	White
Light Color(s)	Red/yellow/green/blue/turquoise/violet/white
Light Function	Permanent

Housing Material	Polycarbonate
Mounting	M30 x 1.5
IP Rating	IP65 and IP69K
NEMA Rating	4X
Connection	5-pin M12 quick-disconnect
Touch to Acknowledge	No
Voltage Rating	10–30 VDC
Requires	5-pin female M12 cable

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/24032050.pdf>
See store item page for other formats.