

24034050 Cut Sheet



WERMA MC55 series LED audible-visual signal beacon, 85 dB at 1m, pulse tone(s), permanent, red/yellow/green/blue/turquoise/violet/white, 55mm, 10–30 VDC, IP65 and IP69K, NEMA 4X. Requires 5-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/24034050>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	MC55
Bulb Type	LED
Operator Size	55mm
Operator Color	White
Light Color(s)	Red/yellow/green/blue/turquoise/violet/white
Light Function	Permanent
Housing Material	Polycarbonate
Material	Polycarbonate

Loudness Decibel	85 dB at 1m
Tone Frequency	3.4 kHz
Tone Type	Pulse
Touch to Acknowledge	No
Voltage Rating	10–30 VDC
Mounting	M30 x 1.5
IP Rating	IP65 and IP69K
NEMA Rating	4X
Connection	5-pin M12 quick-disconnect
Requires	5-pin female M12 cable

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/24034050.pdf>
See store item page for other formats.