

241020 Cut Sheet



RUKO adjustable tap wrench, ratcheting, chrome-plated steel, sliding T-handle. For use with M5 to M12 and 7/32 to 1/2in taps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/241020>

Technical Specifications

Brand	RUKO
Item	Adjustable tap wrench
Ratcheting	Yes
Material	Chrome-plated steel
Handle Type	Sliding T-handle
Chuck	Two-jaw chuck for square shanks
Application	Thread making
For Use With	M5 to M12 and 7/32 to 1/2in taps

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document