

24144055 Cut Sheet



WERMA MC35 series LED audible-visual signal beacon, 80 dB at 1m, continuous tone(s), permanent, red/yellow/green, 35mm, 24 VDC, IP65 and IP69K, NEMA 4X. Requires 5-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/24144055>

Technical Specifications

Brand	WERMA	Loudness Decibel	80 dB at 1m
Item	Audible-visual signal beacon	Tone Frequency	3.4 kHz
Series	MC35	Tone Type	Continuous
Bulb Type	LED	Touch to Acknowledge	No
Operator Size	35mm	Voltage Rating	24 VDC
Operator Color	White	Mounting	M22 x 1.5
Light Color(s)	Red/yellow/green	IP Rating	IP65 and IP69K
Light Function	Permanent	NEMA Rating	4X
Housing Material	Polycarbonate	Connection	5-pin M12 quick-disconnect
Material	Polycarbonate	Requires	5-pin female M12 cable

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/24144055.pdf>
See store item page for other formats.