

244357 Cut Sheet



Stego power cable, input to pigtail, 6.5ft/2m cable length. For use with 0254 series AC LED enclosure lights and Varioline series LED enclosure lights without sockets.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/244357>

Technical Specifications

Brand	Stego
Item	Cable
Cable Type	Power
Replacement	No
Connection 1	Input
Connection 2	Pigtail
Shielded	No
Twisted Pair	No
Cable Length	6.5ft/2m
Conductor Size	15 AWG
For Use With	0254 series AC LED enclosure lights and Varioline series LED enclosure lights without sockets

Agency Approvals

UL Listed File #	None
UL Recognized File #	E90664
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document