

# 244357 Cut Sheet



Stego power cable, input to pigtail, 6.5ft/2m cable length. For use with 0254 series AC LED enclosure lights and Varioline series LED enclosure lights without sockets.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/244357>

## Technical Specifications

|                       |   |
|-----------------------|---|
| <b>Brand</b>          | Stego   |
| <b>Item</b>           | Cable   |
| <b>Cable Type</b>     | Power   |
| <b>Replacement</b>    | No  |
| <b>Connection 1</b>   | Input   |
| <b>Connection 2</b>   | Pigtail   |
| <b>Shielded</b>       | No  |
| <b>Twisted Pair</b>   | No  |
| <b>Cable Length</b>   | 6.5ft/2m  |
| <b>Conductor Size</b> | 15 AWG  |
| <b>For Use With</b>   | 0254 series AC LED enclosure lights and Varioline series LED enclosure lights without sockets |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E90664                                 |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |