

244361 Cut Sheet



Stego power cable, input to pigtail, 6.5ft/2m cable length. For use with DC LED 0254 series enclosure light fixtures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/244361>

Technical Specifications

Brand	Stego
Item	Cable
Cable Type	Power
Replacement	No
Connection 1	Input
Connection 2	Pigtail
Shielded	No
Twisted Pair	No
Cable Length	6.5ft/2m
Conductor Size	15 AWG
For Use With	DC LED 0254 series enclosure light fixtures

Agency Approvals

UL Listed File #	None
UL Recognized File #	E90664
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document