

250 Cut Sheet



Minerallac 2-hole conduit mount strap, standard duty, UL Type UL 1565. Package of 100. For use with 3/4in RMC/IMC/LFMC, 1in tubing, 2/0 AWG SER.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/250>

Technical Specifications

Brand	Minerallac
Item	Strap
Mount Type	Conduit mount
Mounting Holes	2-hole
Mounting Hole Size	3/16in
Duty Rating	Standard duty
Material	Steel
Finish	Pre-galvanized
Outside Diameter	1.00-1.05in
Tubing Size	1in
Rigid Metallic Conduit (RMC) Trade Size	3/4in

Intermediate Metallic Conduit (IMC) Trade Size	3/4in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	3/4in
Service Entrance Wire (SER) Size	2/0 AWG
UL Type	UL 1565
Quantity per Pack	100
For Use With	3/4in RMC/IMC/LFMC, 1in tubing, 2/0 AWG SER

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document