

# 251PRECISION Cut Sheet



Megapro PRECISION multi-bit screwdriver, 13 pieces, rubberized handle with bit storage, 1.8in (46mm) shaft length, Phillips, Torx, hex, slotted, tamperproof torx, spanner and Pentalobe.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/251PRECISION>

## Technical Specifications

<b>Brand</b>	Megapro
<b>Series</b>	PRECISION
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Multi-bit
<b>Number of Pieces</b>	13
<b>Insulated</b>	No
<b>Overall Length</b>	6.3in (160mm)
<b>Shaft Length</b>	1.8in (46mm)
<b>Shaft Diameter</b>	0.30in (7.5mm)
<b>Handle Length</b>	4.5in (114mm)
<b>Handle Type</b>	Rubberized handle with bit storage

<b>Tip Type</b>	Phillips, Torx, hex, slotted, tamperproof torx, spanner and Pentalobe
<b>Includes</b>	(1) rubberized handle with bit storage, (1) hex bit (1.5, 2.0mm), (1) hex bit (2.5, 3.0mm), (1) Pentalobe bit (#2, #5), (1) Phillips bit (#000,#1), (1) Phillips bit (#00, #2), (1) slotted bit (1.5, 2.0mm), (1) slotted bit (2.5, 3.0mm), (1) spanner bit (#2.6, tri-angle #2.3), (1) Torx bit (T4, Torx tamperproof T8), (1) Torx bit (T3, Torx tamperproof T6), (1) Torx bit (T5, Phillips #0), (1) Torx bit (tamperproof T10, T15)
<b>Application</b>	Screwdriving

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>