

251PRECISION Cut Sheet



Megapro PRECISION multi-bit screwdriver, 13 pieces, rubberized handle with bit storage, 1.8in (46mm) shaft length, Phillips, Torx, external hex, slotted, tamperproof torx, spanner, Pentalobe and tri-angle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/251PRECISION>

Technical Specifications

Brand	Megapro
Series	PRECISION
Item	Screwdriver
Screwdriver Type	Multi-bit
Number of Pieces	13
Ratcheting	No
Insulated	No
Lock Mechanism	Ballpoint bit
Overall Length	6.3in (160mm)
Shaft Length	1.8in (46mm)
Shaft Diameter	0.30in (7.5mm)
Handle Length	4.5in (114mm)

Handle Type	Rubberized handle with bit storage
Tip Type	Phillips, Torx, external hex, slotted, tamperproof torx, spanner, Pentalobe and tri-angle
Includes	(1) rubberized handle with bit storage, (1) hex bit (1.5, 2.0mm), (1) hex bit (2.5, 3.0mm), (1) Pentalobe bit (#2, #5), (1) Phillips bit (#000, #1), (1) Phillips bit (#00, #2), (1) slotted bit (1.5, 2.0mm), (1) slotted bit (2.5, 3.0mm), (1) spanner bit (#2.6, tri-angle #2.3), (1) Torx bit (T4, Torx tamperproof T8), (1) Torx bit (T3, Torx tamperproof T6), (1) Torx bit (T5, Phillips #0), (1) Torx bit (tamperproof T10, T15)
Application	Screwdriving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document