

2587-2144 Cut Sheet



WAGO Base series switching power supply, 24 VDC @ 5A/120W, 120 VAC and 240 VAC nominal input, 1-phase, enclosed, metal housing, 35mm DIN rail mount, cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2587-2144>

Technical Specifications

Brand	WAGO
Item	Power supply
Series	Base
Power Supply Type	Switching
Efficiency	88% @ 115 VAC
Output Configuration	Single output
Output	24 VDC @ 5A/120W (adjustable)
Output Voltage Range	23.5–28 VDC
Input voltage range	90–264 VAC
Number of Input Phases	1
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• short circuit

Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Metal
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Cage clamp
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	-30 to +70 °C

Agency Approvals

UL Listed File #	E2558147
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2587-2144.pdf>
See store item page for other formats.