

260 Cut Sheet



Minerallac 2-hole conduit mount strap, standard duty, UL Type UL 1565. Package of 100. For use with 1in RMC/IMC/LFMC, 4/0 AWG SER.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/260>

Technical Specifications

Brand	Minerallac
Item	Strap
Mount Type	Conduit mount
Mounting Holes	2-hole
Mounting Hole Size	3/16in
Duty Rating	Standard duty
Material	Steel
Finish	Pre-galvanized
Outside Diameter	1.30-1.32in
Rigid Metallic Conduit (RMC) Trade Size	1in

Intermediate Metallic Conduit (IMC) Trade Size	1in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1in
Service Entrance Wire (SER) Size	4/0 AWG
UL Type	UL 1565
Quantity per Pack	100
For Use With	1in RMC/IMC/LFMC, 4/0 AWG SER

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document