

# 26300.48006 Cut Sheet



Peter Electronic VSII series compact soft starter, 6A, 200–480 VAC at 3-phase, Trip Class 10, rated for 20 start/hour, internally bypassed, 1 frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/26300.48006>

## Technical Specifications

<b>Brand</b>	Peter Electronic
<b>Item</b>	Soft starter
<b>Controller Type</b>	Compact
<b>Series</b>	VSII
<b>Amperage Rating</b>	6A
<b>Nominal Input Voltage</b>	208 VAC/220-240 VAC/440-480 VAC
<b>Nominal Output Voltage</b>	208 VAC/220-240 VAC/440-480 VAC
<b>Trip Class</b>	Trip Class 10
<b>Starts per Hour</b>	20
<b>Internally Bypassed</b>	Yes
<b>Number of Input Phases</b>	3
<b>Number of Output Phases</b>	3
<b>Number of Controlled Output Phases</b>	3
<b>Control Mode</b>	Sinusoidal

<b>Control Power Requirement</b>	24 VDC
<b>Derating</b>	Unit may require derating for applications other than fans and pumps; see specifications for appropriate derating
<b>Temperature Rating</b>	-10 to +40 °C
<b>Enclosure Type</b>	Enclosed
<b>Mounting</b>	35mm DIN rail, panel or wall
<b>Frame Size</b>	1
<b>IP Rating</b>	IP20
<b>Mains Isolating Relay</b>	No
<b>Output Frequency Range</b>	0–60 Hz
<b>Output Type</b>	SCR output
<b>Reverse Capability</b>	None
<b>SCCR Rating</b>	5 kA SCCR

## Agency Approvals

<b>UL Listed File #</b>	E231693
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/26300.48006.pdf>  
See store item page for other formats.