

# 264011 Cut Sheet

RUKO hand tap, PG-11 x 18, square shank per DIN 10, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/264011>

## Technical Specifications

Brand	RUKO
Item	Hand tap
Thread	PG-11 x 18 conduit per DIN 40430
Thread Length	22mm
Overall Length	3.2in (81mm)
Tap Drill Size	17.35mm
Shank	Square shank per DIN 10
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Thread making

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>