

# 265100UNC Cut Sheet

RUKO machine tap, #10-24 UNC, square shank per DIN 10, reinforced for through threads, 5% cobalt high-speed steel (HSSE-Co5), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/265100UNC>

## Technical Specifications

Brand	RUKO
Item	Machine tap
Thread	#10-24 UNC per ANSI/ASME B1.1
Thread Length	0.63in
Overall Length	2.8in (71mm)
Tap Drill Size	#25 drill size
Shank	Square shank per DIN 10, reinforced for through threads
Material	5% cobalt high-speed steel (HSSE-Co5)
Finish	Bright
For Use On	Stainless steel, brass, steel, aluminum, bronze, plastic and cast iron
Application	Thread making

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>