

# 267072 Cut Sheet



Stego temperature/humidity sensor, -4 to 104 deg F, 40 to 90% RH, 35mm DIN rail mount, 6.5ft/2m cable length. For use with Stego 0309xx-17 & 1309xx-17 heaters.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/267072>

## Technical Specifications

Brand	Stego
Item	Temperature/humidity sensor
Temperature Sensing Range	-4 to 104 deg F
Humidity Sensing Range	40 to 90% RH
Mounting	35mm DIN rail
Cable Length	6.5ft/2m
For Use With	Stego 0309xx-17 & 1309xx-17 heaters

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>