

# 267126 Cut Sheet



Stego temperature/humidity sensor, -4 to 104 deg F, 40 to 90% RH, 35mm DIN rail mount, 9.8ft/3m cable length. For use with Stego 0309xx-17 & 1309xx-17 heaters.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/267126>

## Technical Specifications

|                                  |                                     |
|----------------------------------|-------------------------------------|
| <b>Brand</b>                     | Stego                               |
| <b>Item</b>                      | Temperature/humidity sensor         |
| <b>Temperature Sensing Range</b> | -4 to 104 deg F                     |
| <b>Humidity Sensing Range</b>    | 40 to 90% RH                        |
| <b>Mounting</b>                  | 35mm DIN rail                       |
| <b>Cable Length</b>              | 9.8ft/3m                            |
| <b>For Use With</b>              | Stego 0309xx-17 & 1309xx-17 heaters |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | E234324   |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |