


2687-2142 Cut Sheet



WAGO Eco2 series switching power supply, 24 VDC @ 1.25A/30W (adjustable), 100-240 VAC nominal input, 1-phase, enclosed, plastic housing, 35mm DIN rail mount, cage clamp, NEC Class 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2687-2142>

Technical Specifications

| | |
|------------------------|---|
| Brand | WAGO |
| Item | Power supply |
| Series | Eco2 |
| Power Supply Type | Switching |
| Efficiency | 88% @110VAC |
| Output Configuration | Single output |
| Output | 24 VDC @ 1.25A/30W (adjustable) |
| Output Voltage Range | 22-29 VDC |
| Input voltage range | 90-264 VAC |
| Number of Input Phases | 1 |
| Protection Type(s) | <ul style="list-style-type: none">• overvoltage• short circuit |

| | |
|--------------------------------|-----------------|
| Remote On/Off | No |
| Voltage Monitoring | Yes |
| Enclosure Type | Enclosed |
| Housing Material | Plastic |
| IP Rating | IP20 |
| Mounting | 35mm DIN rail |
| Connector Type | Cage clamp |
| NEC Class 2 | Yes |
| Integrated UPS Battery Control | No |
| Operating Temperature | -25 to 70 deg C |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E255817 |
| UL Recognized File # | None |
| UL Hazardous File # | E198726 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2687-2142.pdf>
See store item page for other formats.