

270 Cut Sheet



Minerallac 2-hole conduit mount strap, standard duty, UL Type UL 1565. Package of 100. For use with 1-1/4in RMC/IMC/LFMC, 1-1/2in EMT, 1-1/2in FMC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/270>

Technical Specifications

Brand	Minerallac	Intermediate Metallic Conduit (IMC) Trade Size	1-1/4in
Item	Strap	Reduced Wall Flexible Metal Conduit Trade Size	1-1/4in
Mount Type	Conduit mount	Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1-1/4in
Mounting Holes	2-hole	UL Type	UL 1565
Mounting Hole Size	1/4in	Quantity per Pack	100
Duty Rating	Standard duty	For Use With	1-1/4in RMC/IMC/LFMC, 1-1/2in EMT, 1-1/2in FMC
Material	Steel		
Finish	Pre-galvanized		
Outside Diameter	1.63-1.73in		
Rigid Metallic Conduit (RMC) Trade Size	1-1/4in		
Electrical Metallic Tubing (EMT) Trade Size	1-1/2in		

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document