

2773-406 Cut Sheet



WAGO 2773 series splicing connector, push-in, side-entry, 6 openings, copper conductor, 20-12 AWG solid, 18-12 AWG stranded, 20A, 600V, polycarbonate housing, transparent/gray. Package of 50.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2773-406>

Technical Specifications

Brand	WAGO
Series	2773
Item	Connector
Connector Type	Splicing
Splice Type	Push-in
Wiring Direction	Side-entry
Number Of Openings	6
Conductor Material (PF)	Copper

Solid Conductor Size	20-12 AWG
Stranded Conductor Size	18-12 AWG
Amperage Rating	20A
Voltage Rating	600V
Housing Material	Polycarbonate
Housing Color	Transparent/gray
Quantity per Pack	50

Agency Approvals

UL Listed File #	E69654, E201573
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2773-406.pdf>
See store item page for other formats.