2787-2134 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

WAGO Pro2 series switching power supply, 12 VDC @ 10A/120W, 120 VAC and 240 VAC nominal input, 1-phase, enclosed, metal housing, 35mm DIN rail mount, cage clamp.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/2787-2134

Technical Specifications

Brand	WAGO
Item	Power supply
Series	Pro2
Power Supply Type	Switching
Efficiency	93.8% @ 110 VAC
Output Configuration	Single output
Output	12 VDC @ 10A/120W (adjustable)
Output Voltage Range	12–14 VDC
Input voltage range	90–264 VAC
Input Voltage Selection Type	Automatic
Number of Input Phases	1
Protection Type(s)	• overvoltage • short circuit

Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Metal
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Cage clamp
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	-25 to +70 °C
Power Boost	150% for 5s

Agency Approvals

UL Listed File #	E255817
UL Recognized File #	None
UL Hazardous File #	E198726
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/2787-2134.pdf
See store item page for other formats.