

27DC3021 Cut Sheet



Socomec SIRCO DC series rotary disconnect switch, load break capable, 3-pole, 600 VDC, 250A, 10kA SCCR, panel mount, UL 98B rated, front operated, accepts 10 x 10mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/27DC3021>

Technical Specifications

Brand	Socomec
Item	Disconnect switch
Series	SIRCO DC
Fusible	No
Load Break Capable	Yes
Number of Poles	3
Voltage Rating	600 VDC
Amperage Rating	250A
SCCR Rating	10kA SCCR

Mounting	Panel
UL Rating	UL 98B rated
Configuration	Front operated
Shaft Size	Accepts 10 x 10mm size shaft
Handle Type	Rotary
Additional Information	Purchase handle separately. Line and load terminal screens and lugs sold separately. NEC Article 690 compliant

Agency Approvals

UL Listed File #	E346418
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	112964
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/27DC3021.pdf>
See store item page for other formats.