

27DC4021 Cut Sheet



Socomec SIRCO DC series rotary disconnect switch, load break capable, 4-pole, 1000 VDC, 250A, 10kA SCCR, panel mount, UL 98B rated, front operated, accepts 10 x 10mm size shaft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/27DC4021>

Technical Specifications

Brand	Socomec
Item	Disconnect switch
Series	SIRCO DC
Fusible	No
Load Break Capable	Yes
Number of Poles	4
Voltage Rating	1000 VDC
Amperage Rating	250A
SCCR Rating	10kA SCCR
Mounting	Panel
UL Rating	UL 98B rated
Configuration	Front operated
Shaft Size	Accepts 10 x 10mm size shaft
Handle Type	Rotary
Additional Information	Purchase handle separately. Line and load terminal screens and lugs sold separately. NEC Article 690 compliant

Agency Approvals

UL Listed File #	E346418
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	112964
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document