

280 Cut Sheet



Minerallac 2-hole conduit mount strap, standard duty, UL Type UL 1565. Package of 100. For use with 1-1/2in RMC/IMC/LFMC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/280>

Technical Specifications

Brand	Minerallac
Item	Strap
Mount Type	Conduit mount
Mounting Holes	2-hole
Mounting Hole Size	1/4in
Duty Rating	Standard duty
Material	Steel
Finish	Zinc plated
Outside Diameter	1.88-1.91in
Rigid Metallic Conduit (RMC) Trade Size	1-1/2in

Intermediate Metallic Conduit (IMC) Trade Size	1-1/2in
Reduced Wall Flexible Metal Conduit Trade Size	1-1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1-1/2in
UL Type	UL 1565
Quantity per Pack	100
For Use With	1-1/2in RMC/IMC/LFMC

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document