

284040-00 Cut Sheet



Stego pressure relief vent plug, M12 x 1.5mm thread type, nickel plated aluminum, 3,667 mL/min @ 70 mBar (1 psi), IP66 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/284040-00>

Technical Specifications

| | |
|------------------------|--------------------------------|
| Brand | Stego |
| Item | Pressure relief vent plug |
| Thread Type | M12 x 1.5mm |
| Thread Length | 9mm |
| Material | Nickel plated aluminum |
| Free Airflow | 3,667 mL/min @ 70 mBar (1 psi) |
| IP Rating | IP66 IP67 |
| Operating Temperature | -20 to +100 deg C |
| Includes | Lock nut |
| Additional Information | Use 17mm wrench size |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/284040-00.pdf>
See store item page for other formats.