

284040-00 Cut Sheet



Stego pressure relief vent plug, M12 x 1.5mm thread type, nickel plated aluminum, 3667 mL/min @ 70 mBar (1 psi), IP66 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/284040-00>

Technical Specifications

Brand	Stego
Item	Pressure relief vent plug
Thread Type	M12 x 1.5mm
Thread Length	9mm
Material	Nickel plated aluminum
Free Airflow	3667 mL/min @ 70 mBar (1 psi)
IP Rating	IP66 IP67
Operating Temperature	-20 to +100 deg C
Includes	Lock nut
Additional Information	Use 17mm wrench size

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document