

# 284200-00 Cut Sheet



Stego pressure compensation plug, M40 snap-in thread type, plastic, light gray, 33,333 mL/min @70mBar (1 psi), IP66 IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/284200-00>

## Technical Specifications

Brand	Stego
Item	Pressure compensation plug
Thread Type	M40 snap-in
Thread Length	15mm
Material	Plastic
Color	Light gray
Free Airflow	33,333 mL/min @70mBar (1 psi)
IP Rating	IP66 IP69K
Operating Temperature	-20 to +70 deg C
Includes	EPDM gasket
Additional Information	40mm hole, panel thickness 1 to 4mm

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>