

28550 Cut Sheet

Viking double-ended drill bit, 7/32in, split point, high-speed steel (HSS), black oxide finish, round shank, 2.6in (66mm) overall length. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/28550>

Technical Specifications

Brand	Viking
Item	Drill bit
Replacement	No
Drill Bit Type	Double-ended
Size	7/32in
Material	High-speed steel (HSS)
Finish	Black oxide
Flute Length	3/4in

Point Angle	135 degrees
Point Cut	Split
Shank Type	Round
Overall Length	2.6in (66mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting
Quantity per Pack	10

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement