

2CLC2024 Cut Sheet



Hammond operator console, NEMA 3R/4/12, 38 x 24 x 20in (HxWxD), freestanding, carbon steel, RAL 7035 light gray, powder coat finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2CLC2024>

Technical Specifications

Brand	Hammond
Item	Operator console
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/12
IP Rating	IP66
Nominal Enclosure Dimensions	38 x 24 x 20in (HxWxD)
Enclosure Height	38.81in
Enclosure Width	24.00in
Enclosure Depth	21.00in
Mounting	Freestanding
Dual Access	No
Knockouts	No

Material	Carbon steel
Color	RAL 7035 light gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Cast hinge with removable pin
Number of Hinges Per Door	2
Number of Lid Hinges	2
Latch Type	1/4-turn semi-flush oil-tight latch
Number of Door Latches	2
Number of Lid Latches	2
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document