

2CSC2048 Cut Sheet



Hammond operator console, NEMA 3R/4/4X/12, 38 x 48 x 20in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 2-door, 1/4-turn semi-flush oil-tight stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2CSC2048>

Technical Specifications

Brand	Hammond
Item	Operator console
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	38 x 48 x 20in (HxWxD)
Enclosure Height	38.81in
Enclosure Width	48.00in
Enclosure Depth	21.03in
Mounting	Freestanding
Dual Access	No

Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Cast hinge with removable pin
Number of Hinges Per Door	2
Number of Lid Hinges	4
Latch Type	1/4-turn semi-flush oil-tight stainless steel latch
Number of Door Latches	4
Number of Lid Latches	3
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document