

# 2PU06MC10 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black and clear blue, double 6mm outside diameter, 5/32in (4mm) inside diameter, 10 coils, 2.8ft (0.86m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2PU06MC10>

## Technical Specifications

Brand	NITRA
Item	Bonded coiled tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Black and clear blue
Outside Diameter	Double 6mm
Inside Diameter	5/32in (4mm)
Number of Coils	10
Working Length	2.8ft (0.86m) working length
Operating Pressure	180 psi
Operating Temperature	-40 to +160 deg F

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>