

2PU08MC40 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black and clear blue, double 8mm outside diameter, 5mm inside diameter, 40 coils, 10.5ft (3.20m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2PU08MC40>

Technical Specifications

Brand	NITRA
Item	Bonded coiled tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Black and clear blue
Outside Diameter	Double 8mm
Inside Diameter	5mm
Number of Coils	40
Working Length	10.5ft (3.20m) working length
Operating Pressure	175 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document