

# 2PU10MC20 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black and clear blue, double 10mm outside diameter, 6.5mm inside diameter, 20 coils, 6.7ft (2.05m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2PU10MC20>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Bonded coiled tubing
<b>Working Fluid</b>	Air or inert gas
<b>Material</b>	Ether-based polyurethane
<b>Color</b>	Black and clear blue
<b>Outside Diameter</b>	Double 10mm
<b>Inside Diameter</b>	6.5mm
<b>Number of Coils</b>	20
<b>Working Length</b>	6.7ft (2.05m) working length
<b>Operating Pressure</b>	150 psi
<b>Operating Temperature</b>	-40 to +160 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>