

# 2PU38-50 Cut Sheet



NITRA pneumatic bonded tubing, ether-based polyurethane, black and clear blue, double 3/8in outside diameter, 0.250in inside diameter, 50ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2PU38-50>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Bonded tubing
<b>Working Fluid</b>	Air or inert gas
<b>Material</b>	Ether-based polyurethane
<b>Color</b>	Black and clear blue
<b>Outside Diameter</b>	Double 3/8in
<b>Inside Diameter</b>	0.250in
<b>Working Length</b>	50ft package
<b>Operating Pressure</b>	150 psi
<b>Operating Temperature</b>	-40 to +160 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>