

2PU38C10 Cut Sheet



NITRA pneumatic bonded coiled tubing, ether-based polyurethane, black and clear blue, double 3/8in outside diameter, 0.250in inside diameter, 10 coils, 3.6ft (1.10m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2PU38C10>

Technical Specifications

| | |
|------------------------------|--------------------------------|
| Brand | NITRA |
| Item | Pneumatic Bonded coiled tubing |
| Material | Ether-based polyurethane |
| Color | Black and clear blue |
| Outside Diameter | Double 3/8in |
| Inside Diameter | 0.250in |
| Number of Coils | 10 |
| Working Length | 3.6ft (1.10m) working length |
| Operating Pressure | 150 psi |
| Operating Temperature | -40 to +160 deg F |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |