

2RL-250 Cut Sheet



Sifam Tinsley AC current transformer, solid core, 25 A primary, 5 A secondary, 1.05 in diameter sensing window, $\pm 5\%$ accuracy, (2) 24 in 16 AWG lead wires.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2RL-250>

Technical Specifications

Brand	Sifam Tinsley
Item	Transformer
Transformer Type	Current
Voltage Type	AC
Body Type	Solid core
Primary Current	25 A
Secondary Current	5 A
Sensing Window	1.05 in diameter
Accuracy	$\pm 5\%$
Secondary Connection Type	(2) 24 in 16 AWG lead wires
Mounting	Pass-through conductor

Agency Approvals

UL Listed File #	None
UL Recognized File #	E472409
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2RL-250.pdf>
See store item page for other formats.